



Philips Smartbright Waterproof G3 batten offers exceptional value. It is perfect for everyday lighting installations.

Available in three standard sizes, it has the option of standard and through-wiring versions.

Smartbright Waterproof G3 WT0 68C

New Smartbright Waterproof Batten G3 provides flexibility with three sizes, standard and through-wiring versions and 2 CCTs to cater to different customer needs

Smartbright Waterproof G3 WTO 68C

Benefits

- Lifetime: 30,000 hrs @ L70B50, 3-year warranty
- IP66, IK06
- Quick connector for easy installation

Features

- 2 colour temperatures, 3 sizes and standard and through-wiring version
- IP66/IK06 – Water and dustproof. For all weather
- Reliable with a long service life of 30,000 hours L70
- 3-year warranty
- Quick connector for easy installation

Application

- Parking Garages
- Offices

Versions



Smartbright Waterproof G3 WTO 68C

Application Conditions

Ambient temperature range -20 to +45 °C

Approval and Application

Mech. impact protection code IK06

Ingress protection code IP66

Controls and Dimming

Dimmable No

Operating and Electrical

Input Voltage 220 to 240 V

General Information

CE mark CE mark

Protection class IEC Safety class II (II)

Optical cover/lens type No

Initial Performance (IEC Compliant)

Init. Colour Rendering Index >80

Initial LED luminaire efficacy 110 lm/W

Luminous flux tolerance +/-10%

Mechanical and Housing

Colour White and grey

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour	Initial luminous flux	Initial input
		Temperature		power
36059199	WT068C CW LED18 L600 PSU	6500 K	1800 lm	16.5 W
36062199	WT068C NW LED18 L600 PSU	4000 K	1800 lm	16.5 W
36060799	WT068C CW LED36 L1200 PSU	6500 K	3600 lm	33 W
36067699	WT068C CW LED56 L1500 PSU	6500 K	5600 lm	51 W
	TW1			

