



Reliable and valuable

SmartBright Panel RC091V 2'X4'

The SmartBright RC091V 2'x4' is an additional dimension in RC091V panel family which satisfies the big size panel demand for GCGM countries. Its valuable with longer lifetime for Edge-lit panels.

Benefits

- 1. Easy to maintain, thanks to 50,000-hour lifetime;
- 2. More bright and comfortable light.
- 3. Flicker-free.

Features

- 48 W, 4,800 lm, 100 lm/W, 4,000 k, 6,500 k, CRI≥80, operating temperature: -10 °C to +35 °C, lifetime: 50,000 hrs @ L70 B50 @Ta 25C, 220-240 V, 50/60 Hz, PF >0.9, Class II
- , Surge protection: DM: 1 KV, CM: 2 KV
- ; 595 x 1,195 x 10 (mm) (height excludes driver)

Application

- Offices, meeting rooms, hospitals, libraries

Warnings and Safety

- 1. The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements. 灯具应由有资格的电工安装，接线要符合 IEE 电气标准或国家标准。 2. Do not switch on before complete installation. 接线过程中，切勿通电。 3. Indoor use only. 灯具只用于室内。 4. The light source of this luminaire is not replaceable; when the light source reaches its end of life, the whole luminaire must be replaced. 此灯具的光源是不可替换的；当光源到其寿终时，应替换整个灯具。 5. The luminaire must not be used or stored in corrosive environment where hazardous materials, such as sulphur, chlorine, phthalates, etc, are present. 本灯具避免存储和使用在腐蚀性环境或者含有有害物质的环境中,例如硫化物,卤化物,邻苯二甲酸酯等。 6. Luminaires not suitable for covering with thermally insulating material. 灯具不适宜被隔热材料覆盖

SmartBright Panel RC091V 2'X4'

Versions

