



Complete range of configurable and connected solar street lights upto 24000 lumens.

RoadFlair Gen 4.0 Solar

Comprehensive range of solar street lights starting from 5000 lumens to 24000 lumens, with 170 lm/w efficacy, and option of hybrid versions. Suitable for major roads, highways and parking areas. configurable dimming profile and load wattage.

Benefits

- Brings light to areas without access to electric grid
- Environment friendly
- Saves energy
- High efficacy reduces cost per light point by reducing battery and panel size
- Preserves landscape as no trenching for cabling required
- Sturdy construction for long life
- Smart city ready for sustainable cities

Features

- High luminous efficacy of 170 lm/Watt.
- Configurable dimming profile and load wattage
- Compatible with multiple battery types (LiFePO4, LMLA GEL)
- Pressure die-cast aluminum housing for sturdiness and excellent thermal management
- Available in both offgrid and hybrid versions

RoadFlair Gen 4.0 Solar

Application

- Highways
- Street
- Road
- Parking

