



# The new Coreline slim batten is slim design and come in 3 sizes and 2 CCT choices based on specific customer needs.

## Coreline Slim Batten

The new Philips Coreline slim batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 3 standard sizes, and 2 CCTs to provide flexibility to customer.

### Benefits

- Slim and Robust design
- 50K Hours Life L70B50
- 5 Years warranty

### Features

- Energy efficient with long service life. (50 000 hours - L70)
- 5 Years Warranty
- IP20, IK04
- CRI80
- 3 Different sizes L600/L1200/L1500 and 2 Different CCT (4000K/6500K) choices

# Coreline Slim Batten

## Application

- Offices
- Residential
- Parking Garages

## Versions



BN126C LED41S L1200






BN126C LED60S L1500



BN126C LED22S L600

## Dimensional drawing



# Coreline Slim Batten

General Information	
CE mark	CE mark
Light Technical	
Correlated Color Temperature (Nom)	4000 K
Optical cover type	Polycarbonate Diffuser
Color rendering index (CRI)	>80
Luminous Efficacy (rated) (Nom)	105 lm/W
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	White RAL 9003
Approval and Application	
Protection class IEC	Safety class I
Mech. impact protection code	IK04
Ingress protection code	IP20/40
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

## Light Technical

Order Code	Full Product Name	Luminous Flux
911401898980	BN126C LED41S/840 PSU L1200	4,100 lm
911401899180	BN126C LED60S/840 PSU L1500	6,000 lm
911401898780	BN126C LED22S/840 PSU L600	2,200 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401898980	BN126C LED41S/840 PSU L1200	31 W
911401899180	BN126C LED60S/840 PSU L1500	46 W

Order Code	Full Product Name	Power Consumption
911401898780	BN126C LED22S/840 PSU L600	17 W

