PHILIPS

Lighting

The new Coreline slim batten is slim design and come in 3 sizes and 2 CCT choices based on specific customer needs.

Coreline Slim Batten

The new Philips Coreline slim batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 3 standard sizes, and 2 CCTs to provide flexibility to customer.

Benefits

- Slim and Robust design
- 50K Hours Life L70B50
- 5 Years warranty

Features

- Energy efficient with long service life. (50 000 hours - L70)
- 5 Years Warranty
- IP20, IK04
- CRI80
- 3 Different sizes L600/L1200/L1500 and 2 Different CCT (4000K/6500K) choices

Coreline Slim Batten

Application


- Offices
- Residential
- Parking Garages


Versions




BN126C LED22S L600

Dimensional drawing







Coreline Slim Batten

General Information	
CE mark	CE mark
Light Technical	
Optical cover type	Polycarbonate Diffuser
Color rendering index (CRI)	>80
Luminous Efficacy (rated) (Nom)	105 lm/W
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	White RAL 9003
Approval and Application	
Protection class IEC	Safety class I
Mech. impact protection code	IK04
Ingress protection code	IP20/40
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Flux
911401898980	BN126C LED41S/840 PSU L1200	4000 K	4,100 lm
911401899080	BN126C LED41S/865 PSU L1200	6500 K	4,100 lm
911401899180	BN126C LED60S/840 PSU L1500	4000 K	6,000 lm
911401899280	BN126C LED60S/865 PSU L1500	6500 K	6,000 lm
911401898780	BN126C LED22S/840 PSU L600	4000 K	2,200 lm
911401898880	BN126C LED22S/865 PSU L600	6500 K	2,200 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401898980	BN126C LED41S/840 PSU L1200	31 W
911401899080	BN126C LED41S/865 PSU L1200	31 W
911401899180	BN126C LED60S/840 PSU L1500	46 W

Order Code	Full Product Name	Power Consumption
911401899280	BN126C LED60S/865 PSU L1500	46 W
911401898780	BN126C LED22S/840 PSU L600	17 W
911401898880	BN126C LED22S/865 PSU L600	17 W

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.