



PHILIPS

GentleSpace 3

BY480P, BY481P



220V
240V

50Hz
60Hz

LEDs



LIFE
L80B50
100K hrs

IP65

GLOW
WIRE
650 °C



W

kg



IK

max



min

BY480P LED130S	84	7.9	IK07	45	-30
BY480P LED170S	120	7.9	IK07	45	-30
BY481P LED250S	162	12	IK07	45	-30
BY481P LED350S	232	12	IK07	45	-30
BY480P LED170S BR	120	8.5	IK07	45	-30
BY481P LED250S BR	162	12.9	IK07	45	-30
BY481P LED250S ELXX	162	12.5	IK07	30	0
BY481P LED350S ELXX BR	232	13.4	IK07	25	0
BY480P LED170S PC	120	7.2	IK08	45	-30
BY481P LED250S PC	162	11	IK08	45	-30

BY480P







BY481P





SMT Standard suspension set




Press button on Express fastener to release




Slide Express fastener up or down on cable to adjust height or release

5




Connect the luminaire to the suspension set



Distance between the hooks		
	BY480P	BY481P
A [mm]	350	495

7




Make sure the load is supported




Mounting bracket set

Mounting bracket set content




x1

x2




x2



x2





x2





16Nm

tightening torque
for all Mounting Bracket screws
in standard applications



BY480P



BY481P

