


Urban

Bracket arm

263 Arm bracket





Ordering Guide

Example: 263 ABS Twist-lock

| Product Code | 263 | Bracket Arm |
|---------------|---|---|
| Finish | ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN IRN RBZ SRT VBZ VCP VGN VTC WBZ | Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White |
| Photo Control | Twist-lock | Twist-lock photocell supplied |

Specifications

CONSTRUCTION:

Cast aluminum decorative end cap (removable). Two cast aluminum post cap. 2" dia. aluminum formed arm. Cast aluminum access door. Cast aluminum 4" I.D. post fitter.

FINISH

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

MOUNTING:

Fixture mounts to 4" I.D. post.

WARRANTY:

Three-year limited warranty.

Height: Width: Max. Weight: 33 7/8" 55"

