


HADCO

by @signify

Landscape

RLL1

RLL1 Step light



Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____

Ordering Guide

Example: RLL1 A

Product Code	RLL1
Finish	A Black

Specifications

HOUSING:

Die-cast aluminum faceplate with galvanized steel, single gang recessed box with stainless steel fasteners. Gasketing is diecut neoprene.

FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

OPTICAL ASSEMBLY:

Frosted tempered glass lens.

LAMPING:

12W maximum S-8 (93) lamp. Lamp is included with fixture.

ELECTRICAL ASSEMBLY:

Single contact bayonet (S-8). 12 volt fixture is pre-wired with 6-ft. pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

Manufactured to ISO 9001:2008 Standards.

Height :

2 13/16" (71mm)

Width:

4 5/8" (116mm)

Depth:

2 3/4" (70mm)

Max. Weight:

1.2 lb

@signify