

**O** kg

0,7

0,7

1,17

1,17

1,17



П



Product info

Model

DN560B DN561B

DN570B

Lumen package

LED12S

LED20S

LED12S

Color Temperature [K]

830/840/927/930/940

830/840/927/930/940

830/840/927/930/940

Printed in Hungary Data subject to change without notice Keep for future reference: www.philips.com/lighting







the manufacturer or his service agent or a similar qualified person

© 2018 Signify Holding.

All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.. All other trademarks are owned by Signify Holding or their respective owners.

Signify Holding. The Netherlands