


Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_



### Ordering Guide

Example: B1 A LED7 NF W S

<b>Product Code</b>	B1	LED Aluminum Bullyte
<b>Finish</b>	A H G	Black Bronze Verde
<b>Source/Lumens</b>	LED7	7W LED
<b>Optics</b>	NF	Narrow Flood
<b>CCT</b>	W	Warm
<b>Shroud</b>	S L	Short Shroud Long Shroud

\*1 Lamp will be shipped with fixture, but not installed. Lamp not sold separately.

### Specifications

#### HOUSING:

Die-cast aluminum. Fully-adjustable swivel arm with vibration-proof locking teeth. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately. Gasketing is silicone. Fasteners are 300 series stainless steel. Shroud is optional.

#### FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

#### OPTICAL ASSEMBLY:

Clear tempered flat glass lens.

#### LAMPING:

7W lamp with 25° beam spread, 25,000 hours life. Color temperature (CCT): warm white (2,700K nominal). No Mercury.

#### ELECTRICAL ASSEMBLY:

Pre-wired with high temperature 18 AWG wire.

#### WARRANTY:

Three-year limited warranty.

#### CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

**Width:** 3 7/8" (98mm)      **Length:** 8 1/2" (216mm)      **Max. Weight:** 1.4 lb.

