



Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Ordering Guide

Example: RLL2 PC

<b>Product Code</b>	RLL2
<b>Finish</b>	PC Natural Copper

### Specifications

**HOUSING:**

Solid copper louvered faceplate with galvanized steel, single gang recessed back box. Fasteners are 300 series stainless steel. Gasketing is diecut neoprene.

**FINISH:**

Natural Copper is bright polished, untreated copper. Color will age naturally to a fine dark copper patina.

**OPTICAL ASSEMBLY:**

Frosted tempered glass lens. Specular aluminum segmented reflector assembly.

**LAMPING:**

12W maximum S-8 (93) lamp. Lower wattage lamps are acceptable. Lamp is included with fixture.

**ELECTRICAL ASSEMBLY:**

Single contact bayonet (S-8). 12 volt fixture is pre-wired with 6-ft. pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

**WARRANTY:**

Three-year limited warranty.

**CERTIFICATIONS:**

Manufactured to ISO 9001:2008 Standards.

**Height :**

2 13/16" (71mm)

**Width:**

4 5/8" (116mm)

**Depth:**

2 3/4" (70mm)

**Max. Weight:**

1.2 lb

