



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering Guide

Example: I3 G H

Product Code	I3	Incandescent	
Rock Guard	G	Rock Guard	*1
Finish	H	Bronze	
	N	Natural Brass	
	SS	Stainless steel (MATTE FINISH)	

*1 Rock guard is optional and available in bronze and natural brass only.

Specifications

HOUSING:

Single-piece compression molded fiberglass reinforced polyester composite, factory pressure tested to ensure water will not wick or leak through. Trim ring is a compression molded polyester. Rock guard used for directional glare control made of compression molded polyester. Single-piece molded silicone U-channel gasket.

FINISH:

Composite is textured, pressure formed, molded-in-color.

OPTICAL ASSEMBLY:

Clear convex, tempered soda-lime glass for high impact resistance. 2,200-pound live-load rated, standard walk-over lens. Lamps have 15° articulation either side of vertical and 358° rotation without interruption of beam pattern.

LAMPING:

100W maximum PAR30/R30 or PAR38/R40 medium base lamp. Lamp is not included. Lower wattage lamps are acceptable.

ELECTRICAL ASSEMBLY:

4kv rated porcelain mini-can base. Nickel-plated screw shell with center contact.

WARRANTY:

Ten-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations.

cETL listed to Canadian safety standards for wet locations.

Manufactured to ISO 9001:2008 Standards.

ADA Compliant when used in concrete and flush mounted with CP3 or CPS3.

IP67 rated to dust tight and sealed against direct jets of water and against prolonged effects of immersion.

Height : 11 1/2" (295mm) **Width:** 9 5/8" (244mm) **Max. Weight:** 9.1 lb.

