

Philips OptiFlood BVP506

Mounting instructions

Instructions de montage
Montageanleitung
Montage Instruktie
Istruzioni di montaggio

Instrucciones de montaje
Instrucces de montagem
Monteringsinstruktioner
Monteringsvejledning

Kokoonpano- ja Kiinnitysohjeet
Montaj yonergesi
Οδηγίες τήξεασομηθιθX
Instrukcja montazu


Szereles utasitasok
Navod k montazi
bycnerwoz gi vjynf:e
Navod k montazi



	COL OUR	LU- MEN	W	min	25°C	35°C	6-10m	•	•	m ²	IK..	IP..	kg
GRN62	657	6568	47	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	19,5
GRN73	657	7658	56	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	19,5
GRN83	657	8723	65	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	19,5
GRN94	657	9851	71	-30°C	15°C	35°C	6-10m	•	•	0,1	09	66	21
GRN104	657	10947	78	-30°C	15°C	35°C	6-10m	•	•	0,1	09	66	21
GRN114	657	12012	87	-30°C	15°C	35°C	6-10m	•	•	0,1	09	66	21
GRN125	657	13136	94	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	21
GRN135	657	14233	103	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	21
GRN146	657	15316	112	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	21
ECO91	657	9495	73	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	19,5
ECO106	657	11085	88	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	19,5
ECO121	657	12654	101	-30°C	15°C	35°C	6-10m	•	•	0,1	09	66	21
ECO136	657	14297	114	-30°C	15°C	35°C	6-10m	•	•	0,1	09	66	21
ECO151	657	15818	127	-30°C	15°C	35°C	6-10m	•	•	0,1	09	66	21
ECO166	657	17400	140	-30°C	35°C	35°C	6-10m	•	•	0,1	09	66	21
ECO181	657	19019	151	-30°C	35°C	35°C	6-10m	•	•	0,1	09	66	21
ECO196	657	20691	165	-30°C	35°C	35°C	6-10m	•	•	0,1	09	66	21
ECO211	657	22170	176	-30°C	35°C	35°C	6-10m	•	•	0,1	09	66	21
ECO226	657	23780	192	-30°C	35°C	35°C	6-10m	•	•	0,1	09	66	21
ECO241	657	25467	204	-30°C	35°C	35°C	6-10m	•	•	0,1	09	66	21
GRN59	740	6199	44	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	19,5
GRN68	740	7207	52	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	19,5
GRN78	740	8194	60	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	19,5
GRN88	740	9246	66	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	21
GRN98	740	10332	73	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	21
GRN107	740	11253	81	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	21
GRN117	740	12399	88	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	21
GRN127	740	13320	95	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	21
GRN137	740	14414	104	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	21
ECO85	740	8948	71	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	19,5
ECO99	740	10412	83	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	19,5
ECO113	740	11850	93	-30°C	15°C	35°C	6-10m	•	•	0,1	09	66	21
ECO127	740	13348	105	-30°C	15°C	35°C	6-10m	•	•	0,1	09	66	21
ECO142	740	14856	119	-30°C	15°C	35°C	6-10m	•	•	0,1	09	66	21
ECO156	740	16339	130	-30°C	25°C	35°C	6-10m	•	•	0,1	09	66	21
ECO170	740	17814	142	-30°C	35°C	35°C	6-10m	•	•	0,1	09	66	21
ECO184	740	19275	153	-30°C	35°C	35°C	6-10m	•	•	0,1	09	66	21
ECO198	740	20825	166	-30°C	35°C	35°C	6-10m	•	•	0,1	09	66	21
ECO212	740	22318	177	-30°C	35°C	35°C	6-10m	•	•	0,1	09	66	21
ECO227	740	23795	190	-30°C	35°C	35°C	6-10m	•	•	0,1	09	66	21
ECO242	740	25308	203	-30°C	35°C	35°C	6-10m	•	•	0,1	09	66	21

220 - 240V
50 - 60Hz

Inrush Current
105A (230v) / 30μs



Disconnect before servicing
Mettre hors tension avant intervention
Öffnen nur spannungsfrei
Demonteren voor onderhoud

Togliere tensione prima di fare manutenzione
Desconectar antes de manipular
Bryt strömmen före lampbyte

PHILIPS

12NC 4413 181 05853
Data subject to change without notice
www.philips.com/lighting

PHILIPS

