

Product Id	Model No.	Classification
PUPR9XUT	APX08LL35-(UNV120208240277)-(MD360WEMLED)	standard
P2MU6RBH	APX08LL35-(UNV120208240277)-A-(MD360WEMLED)	standard
P7Q8JZMS	APX08LL35-(UNV120208240277)-M-(MD360WEMLED)	standard
PUFPFZ5A	APX08LL35-(UNV120208240277)-N-(MD360WEMLED)	standard
PPYY2QP4	APX08LL35-(UNV120208240277)-W-(MD360WEMLED)	standard
P92HV8PR	APX08LL35-347	standard
P3Q83G95	APX08LL35-347-A	standard
PWVSCZ8P	APX08LL35-347-M	standard
PGCRNMBA	APX08LL35-347-N	standard
PTGVCP43	APX08LL35-347-W	standard
PW5NUWDR	APX08LL40-(UNV120208240277)-(MD360WEMLED)	standard
PJTXXA7U	APX08LL40-(UNV120208240277)-A-(MD360WEMLED)	standard
PE1NM8HA	APX08LL40-(UNV120208240277)-M-(MD360WEMLED)	standard
P2SY55YB	APX08LL40-(UNV120208240277)-N-(MD360WEMLED)	standard
PP1VDNJW	APX08LL40-(UNV120208240277)-W-(MD360WEMLED)	standard
PW77E8HW	APX08LL40-347	standard
PTC5KNGC	APX08LL40-347-A	standard
PEWKWCX3	APX08LL40-347-M	standard
PFQ1V642	APX08LL40-347-N	standard
P5USZ3SW	APX08LL40-347-W	standard
PKYCAP5A	APX08LL50-(UNV120208240277)-(MD360WEMLED)	standard
P1JSJ8X2	APX08LL50-(UNV120208240277)-A-(MD360WEMLED)	standard
PGB47YS4	APX08LL50-(UNV120208240277)-M-(MD360WEMLED)	standard
PRKNQKS2	APX08LL50-(UNV120208240277)-N-(MD360WEMLED)	standard
P2R69TUW	APX08LL50-(UNV120208240277)-W-(MD360WEMLED)	standard
PNE59MVE	APX08LL50-347	standard
PP69KDWJ	APX08LL50-347-A	standard
PZ2HWMQR	APX08LL50-347-M	standard
PVKKSX3X	APX08LL50-347-N	standard
PS9JDXB	APX08LL50-347-W	standard
P289G3P1	APX12LL35-(UNV120208240277)-(MD360WEMLED)	standard
PS1FEUCR	APX12LL35-(UNV120208240277)-A-(MD360WEMLED)	standard
PH1DHY6V	APX12LL35-(UNV120208240277)-M-(MD360WEMLED)	standard
PDKNAB21	APX12LL35-(UNV120208240277)-N-(MD360WEMLED)	standard
PWZDCJXN	APX12LL35-(UNV120208240277)-W-(MD360WEMLED)	standard
PH7QSV3E	APX12LL35-347	standard
PNJ6Y9R8	APX12LL35-347-A	standard
PSPQSVTB	APX12LL35-347-M	standard
PQCK4EHT	APX12LL35-347-N	standard
P3RF755G	APX12LL35-347-W	standard
P3XJF57N	APX12LL40-(UNV120208240277)-(MD360WEMLED)	standard
PJ63FNPX	APX12LL40-(UNV120208240277)-A-(MD360WEMLED)	standard
PGT45YDY	APX12LL40-(UNV120208240277)-M-(MD360WEMLED)	standard
PWAUB3X1	APX12LL40-(UNV120208240277)-N-(MD360WEMLED)	standard
P1K6RFT6	APX12LL40-(UNV120208240277)-W-(MD360WEMLED)	standard
PQQP253D	APX12LL40-347	standard
PY9V1YYY	APX12LL40-347-A	standard
PCHZZJ94	APX12LL40-347-M	standard
PHW8W78J	APX12LL40-347-N	standard
PEK1KWX7	APX12LL40-347-W	standard
PSWPRJTD	APX12LL50-(UNV120208240277)-(MD360WEMLED)	standard
PA9FQJGR	APX12LL50-(UNV120208240277)-A-(MD360WEMLED)	standard
PYXG2XAG	APX12LL50-(UNV120208240277)-M-(MD360WEMLED)	standard

Product Id	Model No.	Classification
PD6CU3NV	APX12LL50-(UNV120208240277)-N-(MD360WEMLED)	standard
PUH3N5EP	APX12LL50-(UNV120208240277)-W-(MD360WEMLED)	standard
P977ZV7S	APX12LL50-347	standard
P8HV1Y47	APX12LL50-347-A	standard
P4DYQUWF	APX12LL50-347-M	standard
P32X9JK5	APX12LL50-347-N	standard
PZ6MU1SF	APX12LL50-347-W	standard
PHM54EAQ	APX16LL40-(UNV120208240277)-(MD360WEMLED)	standard
PUB2S2A6	APX16LL40-(UNV120208240277)-A-(MD360WEMLED)	standard
PKS9WU3Q	APX16LL40-(UNV120208240277)-M-(MD360WEMLED)	standard
PKFU78H1	APX16LL40-(UNV120208240277)-N-(MD360WEMLED)	standard
P9K5JUQX	APX16LL40-(UNV120208240277)-W-(MD360WEMLED)	standard
PMBE1DCK	APX16LL40-347-(EMLED)	standard
PNWQ6Q7C	APX16LL40-347-A-(EMLED)	standard
PK9PC639	APX16LL40-347-M-(EMLED)	standard
P8MUJPAE	APX16LL40-347-N-(EMLED)	standard
PMZW5Y7H	APX16LL40-347-W-(EMLED)	standard
PFJ6PJS	APX16LL50-(UNV120208240277)-(MD360WEMLED)	standard
P3JJ5SCY	APX16LL50-(UNV120208240277)-A-(MD360WEMLED)	standard
PXZ7UXH2	APX16LL50-(UNV120208240277)-M-(MD360WEMLED)	standard
PX24BXJQ	APX16LL50-(UNV120208240277)-N-(MD360WEMLED)	standard
P451PXQW	APX16LL50-(UNV120208240277)-W-(MD360WEMLED)	standard
PNTAHQ2P	APX16LL50-347-(EMLED)	standard
PUWEU9PR	APX16LL50-347-A-(EMLED)	standard
PSNPD7RP	APX16LL50-347-M-(EMLED)	standard
PGYTKHYN	APX16LL50-347-N-(EMLED)	standard
P1C158WD	APX16LL50-347-W-(EMLED)	standard
PRXPM99X	APX20LL40-(UNV120208240277)-(MD360WEMLED)	standard
PSNQ2DSR	APX20LL40-(UNV120208240277)-A-(MD360WEMLED)	standard
PBWQCN9N	APX20LL40-(UNV120208240277)-M-(MD360WEMLED)	standard
PWJH6P4C	APX20LL40-(UNV120208240277)-N-(MD360WEMLED)	standard
PC9P7JQF	APX20LL40-(UNV120208240277)-W-(MD360WEMLED)	standard
P9FFSU25	APX20LL40-347-(EMLED)	standard
PG89ARC7	APX20LL40-347-A-(EMLED)	standard
PCRKYT22	APX20LL40-347-M-(EMLED)	standard
P6YH7F5D	APX20LL40-347-N-(EMLED)	standard
P18MY3TY	APX20LL40-347-W-(EMLED)	standard
PBTANDPZ	APX20LL40-480-LFA	standard
PS82D42R	APX20LL50-(UNV120208240277)-(MD360WEMLED)	standard
PNNAS2DP	APX20LL50-(UNV120208240277)-A-(MD360WEMLED)	standard
PHMCXQ8C	APX20LL50-(UNV120208240277)-M-(MD360WEMLED)	standard
PXFB6H5F	APX20LL50-(UNV120208240277)-N-(MD360WEMLED)	standard
P9A8CJV4	APX20LL50-(UNV120208240277)-W-(MD360WEMLED)	standard
P96RV1EU	APX20LL50-347-(EMLED)	standard
PQF6GN38	APX20LL50-347-A-(EMLED)	standard
P7VNP5JN	APX20LL50-347-M-(EMLED)	standard
P19GTUK3	APX20LL50-347-N-(EMLED)	standard
P87W4UNH	APX20LL50-347-W-(EMLED)	standard
P8FH859U	APX24LL40-(UNV120208240277)-(MD360WEMLED)	standard
PUNWPM4U	APX24LL40-(UNV120208240277)-A-(MD360WEMLED)	standard
PXNRSM2B	APX24LL40-(UNV120208240277)-M-(MD360WEMLED)	standard
PVR9DQU1	APX24LL40-(UNV120208240277)-N-(MD360WEMLED)	standard
PYR4YSP2	APX24LL40-(UNV120208240277)-W-(MD360WEMLED)	standard

11/6/2019

Information as of this date. Please check the DLC QPL for confirmation ([www.designlights.org/QPL](http://www.designlights.org/QPL)).

<b>Product Id</b>	<b>Model No.</b>	<b>Classification</b>
PC6UMW1A	APX24LL40-347-(EMLED)	standard
PTE6QK1G	APX24LL40-347-A-(EMLED)	standard
P3QRRZZ5	APX24LL40-347-M-(EMLED)	standard
PUY59QT1	APX24LL40-347-N-(EMLED)	standard
PBEJX836	APX24LL40-347-W-(EMLED)	standard
P8EEBH2Y	APX24LL40-480	standard
PFY88Q9B	APX24LL50-(UNV120208240277)-(MD360WEMLED)	standard
PKTSDH92	APX24LL50-(UNV120208240277)-A-(MD360WEMLED)	standard
P41EPVJK	APX24LL50-(UNV120208240277)-M-(MD360WEMLED)	standard
P9X6MSX1	APX24LL50-(UNV120208240277)-N-(MD360WEMLED)	standard
P6BPNVY8	APX24LL50-(UNV120208240277)-W-(MD360WEMLED)	standard
PA6413DD	APX24LL50-347-(EMLED)	standard
PRPKDPHT	APX24LL50-347-A-(EMLED)	standard
PBCT7WHG	APX24LL50-347-M-(EMLED)	standard
PXNPQFRK	APX24LL50-347-N-(EMLED)	standard
PSBH8KHR	APX24LL50-347-W-(EMLED)	standard