

# HADCO


by @signify

Landscape

Floodlyte

WAMT14 Aluminum

Project: \_\_\_\_\_  
Location: \_\_\_\_\_  
Cat.No: \_\_\_\_\_  
Type: \_\_\_\_\_  
Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
Notes: \_\_\_\_\_



## Ordering Guide

Example: WAMT14 F A

| Product Code | WAMT14 | Aluminum Floodlyte |
|--------------|--------|--------------------|
| Lens         | F      | Frosted Lens *1    |
| Finish       | A      | Black              |
|              | H      | Bronze             |

\*1 Frosted lens is optional.

## Specifications

### HOUSING:

Die-cast aluminum. Gasketing is silicone. Fully-adjustable swivel arm with vibration-proof locking teeth. Fasteners are 300 series stainless steel. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

### FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

### OPTICAL ASSEMBLY:

Clear tempered glass lens.

### LAMPING:

50W maximum T4 halogen. Lamp is included with fixture. Lower wattage lamps are acceptable.

### ELECTRICAL ASSEMBLY:

Bi-pin socket type (GY6.35) with 250° C high temperature teflon coated wire leads. Fixture is pre-wired with 18 AWG black, white, and ground wires. Step-down transformer reduces line voltage to 12 volts. Transformer is potted/encapsulated and features thermal overload protection. Can be used with energy-efficient halogen lamp.

### WARRANTY:

Three-year limited warranty.

### CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

### Height :

7 7/16" (189mm)

### Width:

6 7/8" (175mm)

### Length:

5 1/16" (128mm)

### Max. Weight:

2.17 lb.

@signify