


Floodlight

Designer Floodlight

DF5 - 5"

The Gardco Designer Floodlight DF5 is a small flood luminaire with a choice of (6) precision faceted optical systems. Each is designed to provide a specific distribution and cutoff of stray light. The contemporary soft form die cast housing is available in a variety of finishes creating compatibility with most architectural and landscape elements. The high strength die cast aluminum knuckle features an integral splice compartment eliminating the need for a supplementary junction box and thereby permitting closer to grade mounting.



Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

Ordering Guide

example: DF5CHFLT39CMHE120BRPPCB

Prefix M DF5	lounting	Distribution	Wattage		Voltage	Finis	h	Optio	ns
	Conduit Mount For direct mounting to (2) 1/2" GRC or IMC conduits. No j-box required. J-Box Mount For mounting into 1/2" (1.27cm) hub. Also suitable for direct surface mount to walls or ceilings when fed by EMT, BX, SJO, NM, etc. (For surface mount over outlet box.	 HFL Horizontal Flood T6 / Gl2 lamps only VFL Vertical Flood T6 / Gl2 lamps only HSP Horizontal Spot T6 / Gl2 lamps only NSP Narrow Spot T6 / Gl2 lamps only FLM Fluorescent Medium Fluorescent only WSP Wide Spot Medium base lamps only 	Ceramic Pulse Start MH Electronic Ballast Compact Fluorescent Electronic Ballast High Pressure Sodium Magnetic Ballast	T39CMHE 2.5 T6/G12 Lamp T7OCMHE 2.5 T6/G12 Lamp 32TRF 1.2 42TRF 1.2 50HPS 3.4 E17/Medium Based Lamp	120 277 UNIV Fluoresc and CMH only		Bronze Paint Black Paint White Paint Natural Aluminum Paint Beige Paint Verde Green Paint Optional Color Paint Specify RAL designation ex: OC-RAL7024. Special Color Paint Specify. Must supply color chip.	PCB BD ⁷ CH ⁷ POLY Shield	Button Type Photocontrol Available T70MH, T39/T70CMHE, 32TRF or 42TRF only. Requires actual input voltage when ordered with Fluorescent or CMHE types. Barn Doors Cutoff Hood Polycarbonate lenses carry a 1 year warranty only. Fusing
stanchion pole assembly.									

1. Available with FLM optic only.

2. Fluorescent and CMHE luminaires feature electronic ballasts that accept 120V through 277V, 50hz to 60hz, input. Specify "UNIV" voltage for 120V through 277V.

3. 120V only.

4. Available in WSP optic only.

5. Available in HFL, VFL, HSP or NSP optics only.

6. This footnote is missing on the original spec sheet.

7. Barn Doors (BD) and Cutoff Hoods (CH) are painted to match the luminaire. Either can be used concurrently with the Polycarbonate Shield (POLY) option.

Specifications

HOUSING

A single-piece aluminum housing is die cast in a soft barrel form. A one piece extruded gasket mates with door frame.

DOOR/LENS ASSEMBLY

A heat and impact resistant 1/8" (3.165mm) tempered glass lens and one piece silicone gasket are mechanically secured to door frame.

KNUCKLE

The die cast aluminum knuckle features an integral splice

compartment. A single captive 5/16" (7.9275mm) stainless steel allen-head bolt securely locks the knuckle aiming teeth in 5° increments. An opposite cover plate is removable for access to splices. The knuckle assembly is fully gasketed.

OPTICAL SYSTEM

The wide spot, horizontal flood, vertical flood, horizontal spot, and fluorescent medium optical systems are homogenous sheet and extruded aluminum, electrochemically brightened, anodized and sealed. The narrow spot reflector is hydroformed faceted Alzak® aluminum.

ELECTRICAL

HID UNITS: Each high power factor ballast is capable of providing reliable lamp starting to -20°F/-29°C.

FLUORESCENT UNITS: High power factor electronic ballast standard. Accepts 32w or 42w Triple Tube lamps

FINISH

Each luminaire receives a fade and abrasion resistant,

electrostatically applied, thermally cured textured, polyester powdercoat finish.

LABELS

All luminaires bear UL or CUL (where applicable) Wet Location labels.


WARRANTY


Gardco luminaires feature a 5 year limited warranty. See Warranty Information on www. sitelighting.com for complete details and exclusions. Polycarbonate lenses carry a 1 year warranty only.

Designer Floodlight DF5 - 5"

DF5


Dimensions and Mounting









Note: DF5 knuckle assembly (without any additional hardware) mounts directly to 1" rigid conduit (by others, aprroximately 1.3" O.D.)







* Must be buried in concrete a minimum of 6".



(s) ignify

© 2019 Signify Holding B.V. All rights reserved. Signify reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication. signify.com/outdoorluminaires

Signify, North America Corp., 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216 Signify, Canada Ltd., 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008

www.gardcolighting.c