

# Day-Brite

## CFI

by  Signify

Linear

OWL

Wraparound



## Achieve a balance of performance and appeal

The Day-Brite / CFI LED OWL wraparound is an ideal selection for residential and light commercial applications offering an optimal balance between LED performance and quality of light.



# OWL LED wraparound


## Linear

### Features

- Small profile footprint with performance similar to wider conventional wraparounds
- Hi-lumen 2' options available with similar performance to conventional fluorescent 4'
- 2', 4', and 8' tandem options available
- 50,000hr (L70) LED lumen maintenance<sup>1</sup>
- 5 year warranty based on 25°C ambient<sup>3</sup>
- 80+ CRI
- Diffused acrylic lens provides optimum visual comfort
- DLC listed<sup>4</sup>

### Benefits

- Exceptional long life providing 50,000 hour L70 lumen maintenance<sup>1</sup>
- Superior performance with enhanced diffusion for premium aesthetic appeal
- Ideal use for general illumination in residential and light commercial applications
- 15% or higher energy savings compared to fluorescent<sup>2</sup>



### Ordering guide

Example: OWL240L840-UNV-DIM

Series	Length	Lumens <sup>5</sup>	Color	Voltage	Driver
<b>OWL</b>					
<b>OWL</b> OW LED Wraparound	2 2' length	<b>30L</b> 3000 lumens <b>40L</b> 4000 lumens	<b>850</b> 80 CRI, 5000K <b>840</b> 80 CRI, 4000K <b>835</b> 80 CRI, 3500K	<b>UNV</b> Universal 120/277v <b>347</b> 347V	<b>DIM</b> 0-10v dimming driver <b>SDIM</b> 100/40 step dimming <b>EMLED<sup>7</sup></b> integral emergency battery pack
	4 4' length	<b>40L</b> 4000 lumens			
	8 8' length <sup>6</sup>	<b>50L</b> 5000 lumens <b>70L</b> 7000 lumens			

1. Based on 25°C ambient operating temperature.
2. OWL450L840 input power is 53W vs a 2-light F32T8 HPF ballast at 277V drawing 62W.
3. Visit [www.philips.com/warranties](http://www.philips.com/warranties) for full warranty information.
4. OWL luminaires are Designlights Consortium<sup>®</sup> qualified. Please see the DLC QPL list for exact catalog numbers (<http://www.designlights.org/QPL>).
5. Nominal total delivered lumens.
6. 8' tandem units are double nominal lumens shown. Available in 50L (10,000lm) and 70L (14,000lm) flux packages.
7. EMLED option not available for 347V 5000lm, 7000lm, 8' 10,000lm and 8' 14,000lm, and 2' models.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

