



We couldn't increase  
the speed of light,  
**but we found a way  
to get it to you faster.**

**quickship**

As the complexity of your projects has skyrocketed, fast delivery of your lighting has become increasingly important. The Philips Ledalite 10-day QuickShip program includes all of our high performance and award-winning LED linear, recessed, surface and slot luminaire families.

Please note:

Due to continuing product improvements, Philips Ledalite reserves the right to change product specifications without notice.

Questions?

[CS.ledalite@philips.com](mailto:CS.ledalite@philips.com)








**PHILIPS**





**LEDALITE**



# Philips Ledalite Linear LED

Limit of 500 linear ft per release

	FloatPlane (24)	BoldPlay (78)	Sync (74)	Verge (76)	Jump (12)
Product Family					
Mounting	Curve & Edge Suspended	Suspended	Suspended	Suspended	Suspended/ Surface
Color Temp	3000K, 3500K and 4000K				
Lumen Package	All lumen packages available (varies by product)				
Distribution	Direct/Indirect				Direct
Wiring Configurations*	1cct Dimming (0-10V) • Available Options: Emergency (EM wiring) or Battery Pack				
End Caps (Default)	Sculpted		Flat	Sculpted	

	TruGroove (29)	Sona (77)	MicroSquare (22)	Chopstick (75)
Product Family				
Mounting	Suspended/ Surface	Suspended	Suspended/ Surface	Suspended
Color Temp	3000K, 3500K and 4000K			
Lumen Package	All lumen packages available (varies by product)			
Distribution	Direct, Indirect, Direct/Indirect			Semi-Indirect
Wiring Configurations*	1cct Dimming (0-10V) • Available Options: Emergency (EM wiring) or Battery Pack			
End Caps (Default)	Sculpted		Solid Cube	Flat

## Exclusions:


- Response, Actilume day/occupancy & SpaceWise sensors
- No Battery Pack is available for MicroSquare OR 347V
- Prior **Hold for Release** or **Do Not Ship Before** orders
- All non-standard, 3rd party drivers and components
- Thru-wiring for additional circuits
- Tunable White
- Wall mount




\* **Note:** Not all wiring configurations are available with all LED light source options.  
 White, titanium and black finishes available. All standard optics and downlight kits available.  
**Questions? CS.ledalite@philips.com**



# Philips Ledalite Recessed LED

Limit of 100 units per release

	SilkSpace (42)	VersaForm (41)	ArcForm (36)
Product Family			
Size	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4 & 2x2
Color Temp	3000K, 3500K and 4000K		
Lumen Package	All lumen packages available (varies by product)		
Wiring Configurations*	1cct Dimming (0-10V) • Available Option: Battery Pack		
Ceiling Type			
Standard T-Grid	YES		
Slot/Tegular T-Grid	Not available for this product	YES	
Drywall Kits	YES		
Options	Pre-installed 6' Flex Whips		

	PureFX (94)	Vectra (97)	Shine (33)
Product Family			
Size	1x4 & 2x2	1x4 & 2x2	20"x 2', 20"x 4', 600 x 1200mm, 600 x 600mm
Color Temp	3000K, 3500K and 4000K		
Lumen Package	All lumen packages available (varies by product)		
Wiring Configurations*	1cct Dimming (0-10V) - Available Option: Battery Pack		
Ceiling Type			
Standard T-Grid	YES		
Slot/Tegular T-Grid	YES		Not available for this product
Drywall Kits	YES		Not available for this product
Options	Pre-installed 6' Flex Whips		

## Exclusions:

- All non-standard, 3rd party drivers and components
- Response, Actilume day/occupancy & SpaceWise sensors
- No Battery Pack is available for 347V
- Prior **Hold for Release** or **Do Not Ship Before** orders
- Surface mount versions
- Tunable White & CRI 90
- Chicago housings
- Air Return housings



\*Note: Not all wiring configurations are available with all LED light source options. **Questions?** [CS.ledalite@philips.com](mailto:CS.ledalite@philips.com)

Information current from October, 2017 - Check [ledalite.com](http://ledalite.com) for ongoing updates.



# Philips Ledalite Linear Recessed & Perimeter LED

Limit of 500 linear ft per release

	TruGroove Recessed (39)	TruGroove Perimeter (49)
Product Family		
Mounting	Linear Recessed	Perimeter
Color Temp	3000K, 3500K and 4000K	
Lumen Package	All lumen packages available (varies by product)	
Distribution	Symmetric/Asymmetric	Ambient/Graze
Module Lengths	Row lengths from 2' to 20' in 2' increments	
Wiring Configurations*	1cct Dimming (0-10V) Available Options: Emergency (EM wiring) or Battery Pack	

## Exclusions:

- Response, Actilume day/occupancy & SpaceWise sensors
- Prior **Hold for Release** or **Do Not Ship Before** orders
- No Battery Pack is available for 347V
- All non-standard, 3rd party drivers and components
- Thru-wiring for additional circuits
- Tunable White
- Chicago housings

\*Note: Not all wiring configurations are available with all LED light source options. Questions? [CS.ledalite@philips.com](mailto:CS.ledalite@philips.com)

Information current from October, 2017 - Check [ledalite.com](http://ledalite.com) for ongoing updates.

© 2017 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting North America Corporation  
200 Franklin Square Drive, Somerset, NJ 08873  
Tel. 855-486-2216

Philips Lighting Canada Ltd.  
281 Hillmount Rd, Markham, ON, Canada L6C 2S3  
Tel. 800-668-9008