

HADCO

by @signify

Urban

Manor

5510 Side arm mount

Project:

Location:

Cat.No:

Type:

Lamps:

Qty:

Notes:

No Image
Available

Ordering Guide

Example: 5510 ABS A D 50H E B B

Product Code	5510	Manor	
Finish	ABS	Antique Brass	
	ACP	Antique Copper	
	ARD	Antique Red	
	ASI	Antique Silver	
	BLK	Black	
	BRN	Brown	
	BRZ	Bronze	
	FGN	Forest Green	
	GRA	Granite	
	IRN	Ironstone	
	RBZ	Rustic Bronze	
	SRT	Shadow Rust	
	VBZ	Verde Bronze	
	VCP	Verde Copper	
	VGN	Verde	
	VTC	Vintage Copper	
WBZ	Weathered Bronze		
	WHT	White	
Panel/Globe	A	Clear Acrylic	
	B	Opal Acrylic	
	C	Clear Seeded Acrylic	
	D	Bronze Tone Acrylic	
	E	Clear Textured Acrylic	
	M	Opal Polycarbonate	
	P	Clear Polycarbonate	
	Q	Prismatic Polycarbonate	
Socket	D	Medium	
	G	Mogul	
	L	LED	
	R	Induction	
Wattage/Source	50H	50W MH	*1
	70H	70W MH	
	100H	100W MH	
	35S	35W HPS	*1,2
	50S	50W HPS	
	70S	70W HPS	
	100S	100W HPS	
	100I	100W INC.	*1,2
	55R	55W Induction	*3
	85R	85W Induction	*3
	LED	LED	*3

5510 Manor

Side arm mount

Ordering Guide

Example: 5510 ABS A D 50H E B B

Voltage	E	120V
	F	208V
	G	240V
	H	277V
Distribution	B	6" Type V Distrib.
	C	6" Type III Distrib.
	N	None
Photoeye	B	Button Eye
	N	None

- *1 Medium Base Only
*2 35W HPS and 100W INC (E) 120V Only
*3 Consult Factory

Specifications

CONSTRUCTION:

Cast aluminum finial and cap. Cast aluminum hex roof secures to cage with thumbscrews. Cast aluminum hex cage with cone bottom. Cast aluminum knob. Cast aluminum bracket arm and ballast housing with wall plate.

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

PANELS/LENS/GLOBE:

See lenses for available options.

LAMPING:

Lamp is not included.

ELECTRICAL ASSEMBLY:

Lantern will be prewired and tested. All electrical components are ETL listed.

BALLAST:

Ballast mounted inside moisture proof housing. (Customer must specify wattage and voltage.)

MOUNTING:

See template for dimensions & mounting instructions.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL Listed to U.S. safety standards for wet locations. cETL Listed to Canadian safety standards for wet locations.

Height:

29 3/4"

Width:

14"

Projection:

18 1/8"

Top to Outlet:

22 1/4"

Max. Weight:

