



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering Guide

Example: IL136 G H

Product Code	IL136	Composite Inground	
Rock Guard	G	Rock Guard	*2
Finish	H	Bronze	
	N	Natural Brass	*1

*1 Natural Cast Bronze

Specifications

HOUSING:

Single-piece compression molded fiberglass reinforced polyester composite, factory pressure tested to ensure water will not wick or leak through. Trim ring is a compression molded polyester.

FINISH:

Composite is textured, pressure formed, molded-in-color.

OPTICAL ASSEMBLY:

Lamps have 15° articulation either side of vertical and 358° rotation without interruption of beam pattern. Clear convex, tempered soda-lime glass for high impact resistance. 2,200-pound live-load rated, standard walk-over lens.

LAMPING:

75W maximum PAR 36/AR11 screw terminal lamp. Lower wattage lamps are acceptable.

ELECTRICAL ASSEMBLY:

Double screw terminal socket. 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards. ADA Compliant when flush mounted with CP2 or CPS2.

Height : 8 7/16" (214mm) **Width:** 6 5/8" (169mm) **Max. Weight:** 3.5 lb

