

Project: \_\_\_\_\_


Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_



### Ordering Guide

Example: PTH2170 P3 A

|                      |                       |  |
|----------------------|-----------------------|--|
| <b>Product Code</b>  | PTH2170               | Triple                                     |
| <b>Post diameter</b> | P3<br>P4              | 3" Post Mount<br>4" Post Mount             |
| <b>Finish</b>        | A<br>B<br>G<br>H<br>J | Black<br>White<br>Verde<br>Bronze<br>Green |

### Specifications

**HOUSING:**

356 HM high-strength, low-copper, proprietary cast aluminum alloy .

**FINISH:**

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

**MOUNTING:**

Cast Aluminum Hub mounts to a 3" OD x 3" long (P3) [if applicable] or 4" OD x 6 1/2" long (P4) [if applicable] tenon and is secured with at least (3) 5/16"-18 stainless steel set screws.

**WARRANTY:**

Three-year limited warranty.

**Height :**

17" (43 cm)

**Length:**

42 1/2" (108 cm)

**EPA:**

3.10 sq. ft.

