

# Day-Brite

## CFI

by  Signify

Industrial

FBY

High bay



## Ideal illumination for high performance areas

It has never been easier to find a reliable and cost-friendly solution for your big industrial or institutional spaces. Introducing the new Day-Brite / CFI FBY LED high bay. A superstar with all the flexibility and talent you are looking for.



# “Adaptable like a chameleon...”



**Choose no  
lens, frosted  
or clear**

The Day-Brite/CFI FBY LED high bay provides show-stopping versatility with a wide range of lumen packages and accessories to choose from. Designed for a variety of applications, the FBY is perfect for education facilities, warehouses and retail outlets.





up to  
30,000 lms

3500k  
to  
5000K  
color temp

- 4 powerful lumen packages
- 3 color temperatures
- 7 voltage choices
- 11 options to select from, factory installed for your convenience.
- A variety of useful mounting accessories

# FBY LED high bay


12,000lm, 18,000lm, 24,000lm, & 30,000lm




Standard FBY



FBY W/BSL10LST Option




FBY W/BSL10LST & 347/480V Options



## Ordering guide

Example: **FBY24L840-UNV-LCA**

Family	Lumen Package	Color Temperature	Voltage	Options
<b>FBY</b>				
<b>FBY</b>	<b>12L</b> 12,000 nominal delivered lumens <b>18L</b> 18,000 nominal delivered lumens <b>24L</b> 24,000 nominal delivered lumens <b>30L</b> 30,000 nominal delivered lumens	<b>B35</b> 3500K (CRI 80) <b>B40</b> 4000K (CRI 80) <b>B50</b> 5000K (CRI 80)	<b>UNV</b> Universal voltage 120-277V <b>120</b> 120V <b>208</b> 208V <b>240</b> 240V <b>277</b> 277V <b>347</b> 347V <b>480</b> 480V	<b>WP6<sup>2</sup></b> Wired 6' 16/3 cord & NEMA twist lock plug <b>WC6</b> Wired 6' 16/3 cord <b>WP6D<sup>2</sup></b> Wired 6' 16/3 cord & NEMA twist lock plug for line voltage and wired 6' <b>WC6/4<sup>2</sup></b> Wired 6' 16/4 cord for line voltage plus unswitched hot for BSL10LST <b>WC6/5<sup>2</sup></b> Wired 6' 16/5 cord for line voltage plus 0-10V dimming <b>WC6/6<sup>2</sup></b> Wired 6' 16/6 cord for line voltage plus unswitched hot for BSL10LST <b>BSL10LST<sup>2</sup></b> Factory wired Philips Bodine integral emergency pack, nominal 1100 to 1400 lumens <b>MD360</b> 360° Motion detector (ON/OFF) <b>MD360D</b> 360° Motion detector (ON/DIM to 10%) <b>LCA</b> Clear acrylic lens <b>LFA</b> Frosted acrylic lens



## Accessories (order separately)

- **HNH5-VHOOK** 54" chains & V hooks
- **HCH5-VHOOK** 5' cables & V hooks
- **HCH10-VHOOK** 10' cables & V hooks
- **HCH15-VHOOK** 15' cables & V hooks
- **HCH20-VHOOK** 20' cables & V hooks
- **FBY-PENHGR** Pendant hanger (adds 3" to height)
- **FBY-WG** Wire guard
- **FBX-SLCA-2N** Clear acrylic snap lens
- **FBX-SLFA-2N** Frosted acrylic snap lens

## Footnotes

1. Nominal delivered lumens at 25°C ambient
2. Must specify line voltage
3. Order proper cord option for dimming or emergency

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

