





LUMISTEP



DYNADIMMER



RF / CTC



Philips Iridium gen3 Large (BGP383)

Mounting instructions

Instructions de montage
Montageanleitung
Montage instructie
Istruzioni di montaggio


Instrucciones de montaje
Instruções de montagem
Monteringsinstruktioner
Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet
Montaj yönergesi
Οδηγίες συναμολογησης
Instrukcja montazu

Szerelési utasítások
Návod k montáži
Инструкция по монтажу
Návod k montáži





LINE	LED	W +/- 10%	kg	Inrush current		
GRN 81/830	64	60,6	12	108A/140us	●	●
GRN 91/830	64	69,1	12	108A/140us	●	●
GRN 96/740	64	66,1	12	108A/140us	●	●
GRN 101/830	64	77,5	12	108A/140us	●	●
GRN 106/740	64	74,6	12	108A/140us	●	●
GRN 110/830	64	85,2	12	108A/140us	●	●
GRN 116/740	64	82,4	12	108A/140us	●	●
GRN 120/830	64	95	12	108A/140us	●	●
GRN 125/740	64	90,1	12	108A/140us	●	●
GRN 130/830	64	103,5	12	108A/140us	●	●
GRN 135/740	64	97,9	12	108A/140us	●	●
GRN 140/830	64	112,6	12	108A/140us	●	●
GRN 145/740	64	105,6	12	108A/140us	●	●
GRN 150/830	64	121,6	12	108A/140us	●	●
GRN 155/740	64	114,6	12	108A/140us	●	●
GRN 160/830	64	130,7	12	108A/140us	●	●
GRN 165/740	64	122,7	12	108A/140us	●	●
GRN 175/740	64	130,7	12	108A/140us	●	●
GRN 185/740	64	137,8	12	108A/140us	●	●






4427 101 59162
© 01/2019 Signify Holding. All rights reserved
Data subject to change without notice
Printed in Poland
www.philips.com/lighting






PHILIPS



2 Version without cable




2' Version with cable




SRG10

10kV protection


10A max.



Version SRG10 without cable



Version SRG10 with cable

**4427 101 59162**

© 01/2019 Signify Holding. All rights reserved

Data subject to change without notice

Printed in Poland

www.philips.com/lighting