



# Iridium SGS252/452

## SGS252 SON-T70W II OR PC GR SND

IRIDIUM - SON-T - 70 W - Open CT-POT - Polycarbonate bowl/cover

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs

### Product data

General Information	
Number of light sources	1 [ 1 pc]
Lamp family code	SON-T [ SON-T]
Lamp power	70 W
Kombipack	-
Compensation circuit	-
Gear	CONV [ Conventional]
Optical cover/lens type	PC [ Polycarbonate bowl/cover]
Electrical circuit protection	-
Cable	-
Protection class IEC	Safety class II (II)
Parts color	-
CE mark	CE mark
ENEC mark	ENEC mark
Optic type outdoor	Open CT-POT
Colored frame	-
RAL color	-
Filter coil	-


Product family code	SGS252 [ IRIDIUM]
Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Operating and Electrical	
Input Voltage	230 V
Ignitor	SND [ Digital semi-parallel]
Mechanical and Housing	
Mounting device	No [ -]
Overall height	263 mm
Color	Gray
Dimensions (Height x Width x Depth)	263 x NaN x NaN mm (10.4 x NaN x NaN in)
Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]

## Iridium SGS252/452

Mech. impact protection code	IK08 [ 5 J vandal-protected]
<b>Product Data</b>	
Full product code	871155958852000
Order product name	SGS252 SON-T70W II OR PC GR SND
EAN/UPC - Product	8711559588520
Order code	58852000

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910401815318
Net Weight (Piece)	7.405 kg

### Dimensional drawing



Iridium SGS252

