



Iridium SGS253/453

SGS253 SON-T100W I CR PC GR SND

IRIDIUM, SON-T, 100 W, Closed CT-POT, Polycarbonate bowl/cover

Modular road-lighting luminaires offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs.

Product data

| General Information | |
|--------------------------------|--------------------------|
| Lamp family code | SON-T [SON-T] |
| Gear | CONV [Conventional] |
| Photocell | - |
| Product family code | SGS253 [IRIDIUM] |
| Embedded control | - |
| CE mark | Yes |
| ENEC mark | ENEC mark |
| | |
| Light Technical | |
| Standard tilt angle posttop | 5° |
| Standard tilt angle side entry | 5° |
| Number of light sources | 1 |
| Optical cover type | Polycarbonate bowl/cover |
| Optic type outdoor | Closed CT-POT |
| | |
| Operating and Electrical | |
| Input Voltage | 230 V |
| | |

| Power Consumption | 100 W |
|-------------------------------|--|
| | |
| Mechanical and Housing | |
| Housing Color | Grey |
| Overall height | 289 mm |
| Parts color | - |
| | |
| Approval and Application | |
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK08 [5 J vandal-protected] |
| Protection class IEC | Safety class I |
| | |
| Product Data | |
| Order product name | SGS253 SON-T100W I CR PC GR SND |
| Full product name | SGS253 SON-T100W I CR PC GR SND |
| Full product code | 871155924289700 |
| Order code | 24289700 |
| Material Nr. (12NC) | 910401837118 |
| Numerator - Quantity Per Pack | 1 |


Datasheet, 2023, April 29 data subject to change

Iridium SGS253/453

| EAN/UPC - Product/Case | 8711559242897 |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8711559242897 |


Dimensional drawing













| Product | Α |
|---------------------------------|--------|
| SGS253 SON-T100W I CR PC GR SND | 289 mm |

