



# Iridium SGS253/453

## SGS253 SON-T100W II CR PC GR SND

IRIDIUM, SON-T, 100 W, Closed CT-POT, Polycarbonate bowl/cover

Modular road-lighting luminaires offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs.

### Product data


General Information	
Lamp family code	SON-T [SON-T]
Gear	CONV [Conventional]
Photocell	-
Product family code	SGS253 [IRIDIUM]
Embedded control	-
CE mark	Yes
ENEC mark	ENEC mark
Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Number of light sources	1
Optical cover type	Polycarbonate bowl/cover
Optic type outdoor	Closed CT-POT
Operating and Electrical	
Input Voltage	230 V

Power Consumption	100 W
Mechanical and Housing	
Housing Color	Grey
Overall height	289 mm
Parts color	-
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class II
Product Data	
Order product name	SGS253 SON-T100W II CR PC GR SND
Full product name	SGS253 SON-T100W II CR PC GR SND
Full product code	871155924290300
Order code	24290300
Material Nr. (12NC)	910401837218
Numerator - Quantity Per Pack	1

# Iridium SGS253/453

EAN/UPC - Product/Case	8711559242903
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559242903

## Dimensional drawing



Product	A
SGS253 SON-T100W II CR PC GR SND	289 mm

