



Iridium SGS252/452

SGS252 SON-T70W II CR PC GR SND

IRIDIUM, SON-T, 70 W, Closed CT-POT, Polycarbonate bowl/cover

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs

Product data


| General Information | |
|--------------------------------|--------------------------|
| Lamp family code | SON-T [SON-T] |
| Gear | CONV [Conventional] |
| Product family code | SGS252 [IRIDIUM] |
| CE mark | Yes |
| ENEC mark | ENEC mark |
| Light Technical | |
| Standard tilt angle posttop | 5° |
| Standard tilt angle side entry | 5° |
| Number of light sources | 1 |
| Optical cover type | Polycarbonate bowl/cover |
| Optic type outdoor | Closed CT-POT |
| Operating and Electrical | |
| Input Voltage | 230 V |
| Power Consumption | 70 W |
| Cable | - |

| Mechanical and Housing | |
|-------------------------------|--|
| Housing Color | Grey |
| Mounting device | - |
| Overall height | 263 mm |
| Parts color | - |
| Approval and Application | |
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK08 [5 J vandal-protected] |
| Protection class IEC | Safety class II |
| Product Data | |
| Order product name | SGS252 SON-T70W II CR PC GR SND |
| Full product name | SGS252 SON-T70W II CR PC GR SND |
| Full product code | 871155958855100 |
| Order code | 58855100 |
| Material Nr. (12NC) | 910401839718 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711559588551 |

Iridium SGS252/452

| | |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8711559588551 |

Dimensional drawing



| Product | A |
|---------------------------------|--------|
| SGS252 SON-T70W II CR PC GR SND | 263 mm |

