



Iridium SGS252/452

SGS252 SON-T70W | CR GB GR SND

IRIDIUM - SON-T - 70 W - Closed CT-POT - Glass bowl/cover

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs

Product data

| General Information | |
|-------------------------------|------------------------|
| Number of light sources | 1 [1 pc] |
| Lamp family code | SON-T [SON-T] |
| Lamp power | 70 W |
| Kombipack | - |
| Compensation circuit | - |
| Gear | CONV [Conventional] |
| Optical cover/lens type | GB [Glass bowl/cover] |
| Electrical circuit protection | - |
| Cable | - |
| Protection class IEC | Safety class I (I) |
| Parts color | - |
| CE mark | CE mark |
| ENEC mark | ENEC mark |
| Optic type outdoor | Closed CT-POT |
| Colored frame | - |
| RAL color | - |
| Filter coil | - |
| Product family code | SGS252 [IRIDIUM] |

| Light Technical | |
|-------------------------------------|---|
| Standard tilt angle posttop | 5° |
| Standard tilt angle side entry | 5° |
| Operating and Electrical | |
| Input Voltage | 230 V |
| Ignitor | SND [Digital semi-parallel] |
| Mechanical and Housing | |
| Mounting device | No [-] |
| Overall height | 219 mm |
| Color | Gray |
| Dimensions (Height x Width x Depth) | 219 x NaN x NaN mm (8.6 x NaN x NaN in) |
| Approval and Application | |
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK08 [5 J vandal-protected] |
| Product Data | |
| Full product code | 871155958858200 |


Iridium SGS252/452

| | |
|---------------------------------|--------------------------------|
| Order product name | SGS252 SON-T70W I CR GB GR SND |
| EAN/UPC - Product | 8711559588582 |
| Order code | 58858200 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |

| | |
|---------------------|--------------|
| Material Nr. (12NC) | 910401840018 |
| Net Weight (Piece) | 8.242 kg |



Dimensional drawing



Iridium SGS252

