



Iridium SGS252/452

SGS252 CDO-TT70W I OR PC GR SND

IRIDIUM - MASTER CityWhite CDO-TT - 70 W - Open CT-POT - Polycarbonate bowl/cover

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs

Product data

General Information	
Number of light sources	1 [1 pc]
Lamp family code	CDO-TT [MASTER CityWhite CDO-TT]
Lamp power	70 W
Kombipack	-
Compensation circuit	-
Gear	CONV [Conventional]
Optical cover/lens type	PC [Polycarbonate bowl/cover]
Electrical circuit protection	-
Cable	-
Protection class IEC	Safety class I (I)
Parts color	-
CE mark	CE mark
ENEC mark	ENEC mark
Optic type outdoor	Open CT-POT
Colored frame	-
RAL color	-
Filter coil	-

Product family code	SGS252 [IRIDIUM]
Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Operating and Electrical	
Input Voltage	230 V
Ignitor	SND [Digital semi-parallel]
Mechanical and Housing	
Mounting device	No [-]
Overall height	263 mm
Color	Gray
Dimensions (Height x Width x Depth)	263 x NaN x NaN mm (10.4 x NaN x NaN in)
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]


Iridium SGS252/452

Mech. impact protection code	IK08 [5 J vandal-protected]
Product Data	
Full product code	87115958866700
Order product name	SGS252 CDO-TT70W I OR PC GR SND
EAN/UPC - Product	871159588667
Order code	58866700

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910401840618
Net Weight (Piece)	7.405 kg




Dimensional drawing




Iridium SGS252


Photometric data




OFPC1_SGS252 PC 1xCDO-TT70W OR P1.EPS



OFPC1_SGS252 PC 1xCDO-TT70W OR P2.EPS



OFPC1_SGS252 PC 1xCDO-TT70W OR P4.EPS



OFPC_SGS252 PC 1xCDO-TT70W OR P5X-Polar Outdoor (combined)

Iridium SGS252/452

Photometric data



OFPC_SGS252 PC 1xCDO-TT70W OR P6-Polar Outdoor (combined)

