



Iridium SGS254/454

SGS254 SON-T250W II TP GB GR SND

IRIDIUM, SON-T, 250 W, Open T-POT, Glass bowl/cover

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs

Product data

General Information	
Lamp family code	SON-T [SON-T]
Gear	CONV [Conventional]
Product family code	SGS254 [IRIDIUM]
Embedded control	-
CE mark	Yes
ENEC mark	ENEC mark
Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Number of light sources	1
Optical cover type	Glass bowl/cover
Optic type outdoor	Open T-POT
Operating and Electrical	
Input Voltage	230 V
Power Consumption	250 W
Mechanical and Housing	
Housing Color	Grey


Parts color	-	
Approval and Application		
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]	
Mech. impact protection code	IKO8 [5 J vandal-protected]	
Protection class IEC	Safety class II	
Product Data		
Order product name	SGS254 SON-T250W II TP GB GR SND	
Full product name	SGS254 SON-T250W II TP GB GR SND	
Full product code	871155982517500	
Order code	82517500	
Material Nr. (12NC)	910401873818	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8711559825175	
Numerator - Packs per outer box	1	
EAN/UPC - Case	8711559825175	

Datasheet, 2023, April 29 data subject to change

Iridium SGS254/454


Dimensional drawing













Product	Α
SGS254 SON-T250W II TP GB GR SND	319 mm

