



Iridium SGS254/454

SGS254 SON-T400W II TP GB GR SND

IRIDIUM, SON-T, 400 W, Open T-POT, Glass bowl/cover


Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs.

Product data

General Information		Approval and Application	
Lamp family code	SON-T [SON-T]	Protection class IEC	Safety class II
Product family code	SGS254 [IRIDIUM]		
CE mark	Yes	Product Data	
		Order product name	SGS254 SON-T400W II TP GB GR SND
		Full product name	SGS254 SON-T400W II TP GB GR SND
		Full product code	871155982522900
		Order code	82522900
		Material Nr. (12NC)	910401874318
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711559825229
		Numerator - Packs per outer box	1
		EAN/UPC - Case	8711559825229
Light Technical			
Optical cover type	Glass bowl/cover		
Optic type outdoor	Open T-POT		
Operating and Electrical			
Power Consumption	400 W		
Mechanical and Housing			
Housing Color	Gray		

Iridium SGS254/454

Dimensional drawing



Product	A
SGS254 SON-T400W II TP GB GR SND	319 mm

