



Iridium SGS254/454

SGS254 SON-T250W II CP GB GR SND

IRIDIUM, SON-T, 250 W, Closed T-POT, Glass bowl/cover

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs.


Product data

General Information	
Lamp family code	SON-T [SON-T]
Product family code	SGS254 [IRIDIUM]
CE mark	Yes
Light Technical	
Optical cover type	Glass bowl/cover
Optic type outdoor	Closed T-POT
Operating and Electrical	
Power Consumption	250 W
Mechanical and Housing	
Housing Color	Gray

Approval and Application	
Protection class IEC	Safety class II
Product Data	
Order product name	SGS254 SON-T250W II CP GB GR SND
Full product name	SGS254 SON-T250W II CP GB GR SND
Full product code	871155982537300
Order code	82537300
Material Nr. (12NC)	910401875818
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559825373
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559825373

Iridium SGS254/454

Dimensional drawing



Product	A
SGS254 SON-T250W II CP GB GR SND	319 mm

