



Iridium SGS254/454

SGS254 SON-T250W II CP GB GR SND

IRIDIUM - SON-T - 250 W - Closed T-POT - Glass bowl/cover

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs.

Product data

General Information	
Lamp family code	SON-T [SON-T]
Lamp power	250 W
Optical cover/lens type	GB [Glass bowl/cover]
Protection class IEC	Safety class II (II)
Optic type outdoor	Closed T-POT
Product family code	SGS254 [IRIDIUM]


Operating and Electrical	
Ignitor	SND [Digital semi-parallel]

Mechanical and Housing	
Color	Gray
Dimensions (Height x Width x Depth)	NaN x NaN x NaN mm (NaN x NaN x NaN in)

Product Data	
Full product code	871155982537300
Order product name	SGS254 SON-T250W II CP GB GR SND
EAN/UPC - Product	8711559825373
Order code	82537300
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910401875818
Net Weight (Piece)	14.887 kg


Iridium SGS254/454

Dimensional drawing



Iridium SGS254

Photometric data



OFPC1_SGS254 GB 1xSON-TPP250W CP P3X.EPS

