



# Lineco TMS022

## TMS022 1xTL-D58W HF

TMS022, 1, MASTER TL-D, 58 W, Electronic high-frequency

Functional and economical general-purpose basic batten for TL-D fluorescent lamp(s) with choice of two optics for symmetrical or asymmetrical lighting. For surface mounting. A repositionable contact block makes a flexible connection possible and keeps the installation costs low.


### Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HF [Electronic high-frequency]
Product family code	TMS022 [TMS022]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
Light Technical	
Number of light sources	1
Optic type	-
Operating and Electrical	
Input Voltage	230 to 240 V
Power Consumption	58 W
Mechanical and Housing	
Fixation point length distance (Nom)	900 mm
Overall length	1,525 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TMS022 1xTL-D58W HF
Full product name	TMS022 1xTL-D58W HF
Full product code	871829104533599
Order code	04533599
Material Nr. (12NC)	910402269603
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291045335
Numerator - Packs per outer box	9
EAN/UPC - Case	8718291044871

Lineco TMS022

Dimensional drawing



Product
TMS022 1xTL-D58W HF

