



SGS203/403

SGS203 SON-TPP250W K 230V ST

SGS203, SON-T PIA Plus, 250 W, 230 V

SGS203/403 is a modular luminaire in contemporary style for safe and comfortable driving, and for area illumination, with low energy and maintenance costs. It offers a choice of canopies and a bowl or minimal-glare flat glass. Dedicated optics optimize beam control and maximize light output. Five different reflector positions allow precise control of beam direction. Energy savings are possible, for instance with the Chronosense dimming system (no pilot cable required). SGS203/403 is suitable for side-entry or post-top mounting.

Product data

General Information	
Lamp family code	SON-TPP [SON-T PIA Plus]
Gear	CONV [Conventional]
Photocell	-
Product family code	SGS203 [SGS203]
Embedded control	-
CE mark	Yes
ENEC mark	ENEC mark
Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Number of light sources	1
Optical cover type	Polycarbonate bowl/cover
Optic type outdoor	-
Operating and Electrical	
Input Voltage	230 V


Power Consumption	250 W
Connection	-
Cable	-
Mechanical and Housing	
Housing Color	Grey
Mounting device	-
Parts color	-
Approval and Application	
Ingress protection code	IP43 [Wire-protected, rain/spray-proof]
Protection class IEC	Safety class I
Product Data	
Order product name	SGS203 SON-TPP250W K 230V ST
Full product name	SGS203 SON-TPP250W K 230V ST
Full product code	871155972246700
Order code	72246700

SGS203/403

Material Nr. (12NC)	910403063112
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559722467
Numerator - Packs per outer box	1

EAN/UPC - Case	8711559722467
----------------	---------------

Dimensional drawing



Product
SGS203 SON-TPP250W K 230V ST

