



SGS203/403

SGS203 SON-TPP50W K 230V FG ST

SGS203 – SON-T PIA Plus – 50 W – Lamp(s) included – 230 V – Flat glass – Semi-parallel self-stopping

SGS203/403 is a modular luminaire in contemporary style for safe and comfortable driving, and for area illumination, with low energy and maintenance costs. It offers a choice of canopies and a bowl or minimal-glare flat glass. Dedicated optics optimize beam control and maximize light output. Five different reflector positions allow precise control of beam direction. Energy savings are possible, for instance with the Chronosense dimming system (no pilot cable required). SGS203/403 is suitable for side-entry or post-top mounting.

Product data

General Information		Operating and Electrical	
Number of light sources	1 [1 pc]	ENEC mark	ENEC mark
Lamp family code	SON-TPP [SON-T PIA Plus]	Filter coil	-
Lamp power	50 W	Photocell	No [-]
Kombipack	Lamp(s) included	Product Family Code	SGS203 [SGS203]
Gear	CONV [Conventional]	Light Technical	
Optical cover/lens type	FG [Flat glass]	Standard tilt angle post-top	5°
Embedded control	No [-]	Standard tilt angle side entry	5°
Light regulation	-	Operating and Electrical	
Separate switching	-	Input voltage	230 V
Electrical circuit protection	-	Ignitor	ST [Semi-parallel self-stopping]
Connection	No [-]	Mechanical and Housing	
Cable	-	Mounting device	No [-]
Protection class IEC	Safety class I (I)		
Parts colour	-		
CE mark	CE mark		

SGS203/403

Colour	Gray	Order code	72247400
Approval and Application		Numerator – quantity per pack	1
Ingress protection code	IP43 [Wire-protected, rain/spray-proof]	Numerator – packs per outer box	1
Product Data		Material no. (12NC)	910403063212
Full product code	871155972247400	Net weight (piece)	5.694 kg
Order product name	SGS203 SON-TPP50W K 230V FG ST		
EAN/UPC – product	8711559722474		



Dimensional drawing

SGS203/403

