



# SGS203/403

## SGS203 SON-TPP70W K 230V FG ST

SGS203, SON-T PIA Plus, 70 W, 230 V, Flat glass

SGS203/403 is a modular luminaire in contemporary style for safe and comfortable driving, and for area illumination, with low energy and maintenance costs. It offers a choice of canopies and a bowl or minimal-glare flat glass. Dedicated optics optimize beam control and maximize light output. Five different reflector positions allow precise control of beam direction. Energy savings are possible, for instance with the Chronosense dimming system (no pilot cable required). SGS203/403 is suitable for side-entry or post-top mounting.

### Product data


General Information		Power Consumption	
Lamp family code	SON-TPP [SON-T PIA Plus]	Power Consumption	70 W
Gear	CONV [Conventional]	Connection	-
Photocell	-	Cable	-
Product family code	SGS203 [SGS203]	Mechanical and Housing	
Embedded control	-	Housing Color	Grey
CE mark	Yes	Mounting device	-
ENEC mark	ENEC mark	Overall height	200 mm
		Parts color	-
Light Technical		Approval and Application	
Standard tilt angle posttop	5°	Ingress protection code	IP43 [Wire-protected, rain/spray-proof]
Standard tilt angle side entry	5°	Protection class IEC	Safety class I
Number of light sources	1	Product Data	
Optical cover type	Flat glass	Order product name	SGS203 SON-TPP70W K 230V FG ST
Optic type outdoor	-	Full product name	SGS203 SON-TPP70W K 230V FG ST
Operating and Electrical		Full product code	871155972248100
Input Voltage	230 V		

# SGS203/403

Order code	72248100
Material Nr. (12NC)	910403063312
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559722481

Numerator - Packs per outer box	1
EAN/UPC - Case	8711559722481

## Dimensional drawing



Product	A
SGS203 SON-TPP70W K 230V FG ST	200 mm

