



SGS203/403

SGS203 SON-TPP100W K 230V FG ST

SGS203, SON-T PIA Plus, 100 W, 230 V, Flat glass

SGS203/403 is a modular luminaire in contemporary style for safe and comfortable driving, and for area illumination, with low energy and maintenance costs. It offers a choice of canopies and a bowl or minimal-glare flat glass. Dedicated optics optimize beam control and maximize light output. Five different reflector positions allow precise control of beam direction. Energy savings are possible, for instance with the Chronosense dimming system (no pilot cable required). SGS203/403 is suitable for side-entry or post-top mounting.


Product data

General Information		Cable	
Lamp family code	SON-TPP [SON-T PIA Plus]	-	
Gear	CONV [Conventional]		
Photocell	-	Mechanical and Housing	
Product family code	SGS203 [SGS203]	Mounting device	
Embedded control	-	-	
CE mark	Yes	Overall height	
ENEC mark	ENEC mark	200 mm	
		Parts color	
		-	
Light Technical		Approval and Application	
Number of light sources	1	Ingress protection code	
Optical cover type	Flat glass	IP43 [Wire-protected, rain/spray-proof]	
Optic type outdoor	-	Protection class IEC	
		Safety class I	
Operating and Electrical		Product Data	
Input Voltage	230 V	Order product name	
Power Consumption	100 W	SGS203 SON-TPP100W K 230V FG ST	
Connection	-	Full product name	
		SGS203 SON-TPP100W K 230V FG ST	
		Full product code	
		871155972249800	
		Order code	
		72249800	
		Material Nr. (12NC)	
		910403063412	
		Numerator - Quantity Per Pack	
		1	

SGS203/403

EAN/UPC - Product/Case	8711559722498
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559722498

Dimensional drawing



Product	A
SGS203 SON-TPP100W K 230V FG ST	200 mm

