



TrueLine, recessed

RC530Z EP WH SET (2PCS)

TrueLine ACC - End piece - White - Set of 2 units

Architects need a lighting solution that matches the interior architecture of the property they are working on. They want a light line with an elegant design and very high light levels. Specifiers need luminaires that enable them to save energy while at the same time providing the right level of light, in compliance with office lighting norms. TrueLine, recessed is able to meet both sets of requirements. TrueLine is also available in a suspended version.

Product data

General Information	
Protection class IEC	Safety class I (I)
CE mark	CE mark
UL mark	-
Material	Steel
Suspension accessories	No [-]
Mechanical accessories	EP [End piece]
Packaging configuration	SET [Set of 2 units]
Angle	-
Accessory colour	White
Accessory PFC	RC530Z
Product Family Code	RC530Z [TrueLine ACC]
Operating and Electrical	
Input voltage	- V
Input frequency	0 Hz
Mechanical and Housing	
Length	75 mm

Width	42 mm
Diameter	-
Dimensions (height x width x depth)	NaN x NaN x NaN mm (NaN x NaN x NaN in)

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Product Data

Full product code	871869687480699
Order product name	RC530Z EP WH SET (2PCS)
EAN/UPC – product	8718696874806
Order code	87480699
Numerator – quantity per pack	1
Numerator – packs per outer box	20
Material no. (12NC)	910403219703
Net weight (piece)	82.000 g



Warnings and Safety

