



# TrueLine, recessed

## RC530Z EP WH SET ( 2PCS)

TrueLine ACC, White

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine recessed is rated  $UGR < 19$ , which is compliant with all office norms (OC). TrueLine also comes in suspended and surface-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 140 lm/W and the option to upgrade to wireless connectivity and control.

### Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

### Product data

General Information	
Angle	-
Accessory color	White
Service tag	Yes
Product family code	RC530Z [TrueLine ACC]

Value ladder	Specification
Operating and Electrical	
Input Voltage	- V
Line Frequency	0 Hz

TrueLine, recessed

Mechanical and Housing	
Overall length	45 mm
Overall width	75 mm
Overall height	78 mm
Dimensions (Height x Width x Depth)	78 x 75 x 45 mm
Material	Steel
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Product Data	
Order product name	RC530Z EP WH SET ( 2PCS)
Full product name	RC530Z EP WH SET ( 2PCS)
Full product code	871869687480699
Order code	910403219703
Material Nr. (12NC)	910403219703
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696874806
Numerator - Packs per outer box	20
EAN/UPC - Case	8718696871317

