



# LED Bollard II

## BCP150 LED150/NW PSU 220-240V 9006

LED Low Power - 740 neutral white - Power supply unit - 220 to 240 V

People want to create a pleasant atmosphere around their property – something that will catch visitors’ attention, make them feel good and want to come back again. They would like to be able to create an appealing ambience with optimized-quality lighting at minimum cost. Combining reliable low-power LEDs and an integrated driver, the robustly designed LED Bollard II delivers an affordable LED lighting solution to meet your landscaping needs.

### Product data

General Information	
Number of light sources	1 [ 1 pc]
Lamp family code	LED-LP [ LED Low Power]
Lamp colour code	740 neutral white
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	PSU [ Power supply unit]
Driver included	Yes
Optical cover/lens type	PC-UV [ Polycarbonate bowl/cover UV-resistant]
Embedded control	No [ -]
Control interface	-
Connection	Screw connection block
Cable	Cable without plug 3-pole
Protection class IEC	Safety class I (I)
Flammability mark	F [ For mounting on normally flammable surfaces]
CE mark	CE mark
Warranty period	1 years

RAL colour	White aluminum (9006)
Constant light output	No
Number of products on MCB	1
LED engine type	LED

Operating and Electrical	
Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Power factor (min.)	0.4

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Housing material	Aluminum extruded
Optical cover/lens material	Polycarbonate
Mounting device	Baseplate

## LED Bollard II

Optical cover/lens finish	Matte
Overall height	500 mm
Overall diameter	180 mm
Colour	Aluminium and White

### Approval and Application

Ingress protection code	IP65 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [ 20 J vandal-resistant]

### Initial Performance (IEC Compliant)

Initial luminous flux	200 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	28.57 lm/W
Lamp colour temperature	4000 K
Colour Rendering Index	>70
Initial input power	7 W
Power consumption tolerance	+/-10%

### Application Conditions


Ambient temperature range	-20 to +40 °C
---------------------------	---------------

### Product Data

Full product code	910403308002
Order product name	BCP150 LED150/NW PSU 220-240V 9006
EAN/UPC – product	8710163278919
Order code	910403308002
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910403308002
Net weight (piece)	1.320 kg



## Dimensional drawing



LED Bollard II BCP150/151

