



LED Bollard II

BCP151 LED150/NW PSU 220-240V 7043

LED Low Power - 740 neutral white - Power supply unit - 220 to 240 V

People want to create a pleasant atmosphere around their property – something that will catch visitors’ attention, make them feel good and want to come back again. They would like to be able to create an appealing ambience with optimized-quality lighting at minimum cost. Combining reliable low-power LEDs and an integrated driver, the robustly designed LED Bollard II delivers an affordable LED lighting solution to meet your landscaping needs.

Product data

General Information	
Number of light sources	1 [1 pc]
Lamp family code	LED-LP [LED Low Power]
Lamp colour code	740 neutral white
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Optical cover/lens type	PC-UV [Polycarbonate bowl/cover UV-resistant]
Embedded control	No [-]
Control interface	-
Connection	Screw connection block
Cable	Cable without plug 3-pole
Protection class IEC	Safety class I (I)
Flammability mark	F [For mounting on normally flammable surfaces]
CE mark	CE mark
Warranty period	1 years

RAL colour	Traffic gray B (7043)
Constant light output	No
Number of products on MCB	1
LED engine type	LED

Operating and Electrical

Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Power factor (min.)	0.4

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Aluminum extruded
Optical cover/lens material	Polycarbonate
Mounting device	Baseplate

LED Bollard II

Optical cover/lens finish	Matte
Overall height	800 mm
Overall diameter	180 mm
Colour	Dark Grey

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]

Initial Performance (IEC Compliant)

Initial luminous flux	200 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	28.57 lm/W
Lamp colour temperature	4000 K
Colour Rendering Index	>70
Initial input power	7 W
Power consumption tolerance	+/-10%

Application Conditions


Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Product Data

Full product code	910403308202
Order product name	BCP151 LED150/NW PSU 220-240V 7043
EAN/UPC – product	8710163278933
Order code	910403308202
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910403308202
Net weight (piece)	1.850 kg



Dimensional drawing



LED Bollard II BCP150/151

