



TCW060 C

TCW060 C 1xTL-D36W HF 220V

1, MASTER TL-D, 36 W, Electronic high-frequency, 220 V


Designed for use in demanding environments, TCW060 is an economical, compact waterproof luminaire. Dedicated versions are available for TL-D and TL5 lamps. Ingress-protected to a level of IP65 and operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces – at the same cost as an electromagnetic solution. A flexible ceiling clip facilitates easy installation and maintenance.

Product data

General Information		Full product name	TCW060 C 1xTL-D36W HF 220V
Lamp family code	TL-D [MASTER TL-D]	Full product code	910403630028
Gear	HF [Electronic high-frequency]	Order code	910403630028
Light Technical		Material Nr. (12NC)	910403630028
Number of light sources	1	Numerator - Quantity Per Pack	1
Operating and Electrical		EAN/UPC - Product/Case	6923828687373
Input Voltage	220 V	Numerator - Packs per outer box	9
Power Consumption	36 W	EAN/UPC - Case	6923828698928
Product Data			
Order product name	TCW060 C 1xTL-D36W HF 220V		

TCW060 C

Dimensional drawing



Product	A	B
TCW060 C 1xTL-D36W HF 220V	900 mm	1,270 mm

