



# Vandalite TCW098

## TCW098 1xTL5 14W K HFS OP

1, TL5, 14 W, HF Standard

Vandalite is a surface mounted fluorescent luminaire that, as its name implies, is a tough, dust and watertight product for situations where semi-outdoor exposure and vandalism can be a problem. The Vandalite has an IP65 rating, being totally dustproof and waterproof. Its robust construction makes it virtually vandal-proof. The body is injection moulded, glass filled nylon for long life and added strength. The reflector is of pressed prepainted steel with integral gear and rota-lock lampholders for 1xTL5 14W lamp or with moulding and posts for 2xPL 18W or 1xPL 36W lamps.

### Product data

General Information		Product Data	
Lamp family code	TL5 [TL5]	Order product name	TCW098 1xTL5 14W K HFS OP
Gear	HFS [HF Standard]	Full product name	TCW098 1xTL5 14W K HFS OP
<b>Light Technical</b>		Local code description	TCW098114T5OP
Number of light sources	1	Order code	910403630085
<b>Operating and Electrical</b>		Material Nr. (12NC)	910403630085
Input Voltage	220 V	Local order code	TCW098114T5OP
Line Frequency	50 Hz	Numerator - Quantity Per Pack	1
Power Consumption	14 W	EAN/UPC - Product/Case	8710163291291
<b>Approval and Application</b>		Numerator - Packs per outer box	8
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]	EAN/UPC - Case	8710163291321
Protection class IEC	Safety class I		

## Vandalite TCW098

### Dimensional drawing

