



Aurora SPP202

SPP202 SON-T150W 240V-50Hz GB RAL7040

SON-T, 150 W, 240 V, 50 Hz, Glass bowl/cover

The Philips Aurora range of street light luminaires brings a new quality of light to residential areas, cycle paths, local roads and industrial estates. Aurora unites superior optics, a weather-proof housing and easy maintenance. Moreover, its sleek shape combining a variety of attractive pole designs and compact size make a significant contribution to a pleasant and more comfortable environment while being cost efficient.

Product data

General Information		Approval and Application	
Lamp family code	SON-T [SON-T]	Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Gear	CONV [Conventional]		
Light Technical		Product Data	
Number of light sources	1	Order product name	SPP202 SON-T150W 240V-50Hz GB RAL7040
Optical cover type	Glass bowl/cover	Full product name	SPP202 SON-T150W 240V-50Hz GB RAL7040
Operating and Electrical		Full product code	910403630148
Input Voltage	240 V	Order code	03630148
Line Frequency	50 Hz	Material Nr. (12NC)	910403630148
Power Consumption	150 W	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1

Aurora SPP202

Dimensional drawing

