



# Smart Halogen Downlight QBS020

QBS048 1xMAX50W/12V-GU5.3 WH

1, GU5.3, White

Shop owners opening a new outlet or refurbishing their current installation and contractors looking for attractive propositions for their customers (small/non-chain retailers) now have the ideal solution for impactful, yet affordable accent lighting. Our Smart Halogen Downlight offers customers a choice of different shapes to suit different functions, and the professional finish lends the luminaire an air of contemporary sophistication. Thanks to its robust housing, the Smart Halogen Downlight is a long-lasting solution. Quality clips ensure ease of installation.

## Product data

General Information		Temperature	
Cap-Base	GU5.3 [GU5.3]	Ambient temperature range	-10 to +35 °C
Lighting Technology	LED	Mechanical and Housing	
Light Technical		Housing Color	White
Number of light sources	1	Overall length	33 mm
Luminaire light beam spread	108°	Overall width	170 mm
Operating and Electrical		Overall height	170 mm
Input Voltage	12 V	Dimensions (Height x Width x Depth)	170 x 170 x 33 mm
Line Frequency	50 to 60 Hz	Approval and Application	
Input Frequency	50 to 60 Hz	Ingress protection code	IP20 [Finger-protected]
		Mech. impact protection code	IK03 [0.3 J]
		Protection class IEC	Safety class II

# Smart Halogen Downlight QBS020

Product Data	
Order product name	QBS048 1xMAX50W/12V-GU5.3 WH
Full product name	QBS048 1xMAX50W/12V-GU5.3 WH
Full product code	910403630294
Order code	910403630294
Material Nr. (12NC)	910403630294

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828687847
Numerator - Packs per outer box	30
EAN/UPC - Case	6923828699390

## Dimensional drawing

