



Iridium² Medium

SGP352 CPO-TW60W K EB FX1 AL GR

Iridium² Medium, MASTER CosmoWhite CPO-TW, 60 W,
Electronic, Flexible distribution version 1, Grey

Iridium² is a family of road lighting luminaires designed for performance and sustainability. Depending on the application and budget, customers can start with LED, electronic HID or a mix of both technologies with the same luminaire. Whatever the initial choice, Iridium²'s modularity allows customers to upgrade their installations (LED to LED or e-HID to LED) whenever they want, simply by changing the light engine. The integration of LEDGINE, brand new HID optics, electronic gear and controls is a response to the growing demand for energy savings. The new Iridium² HID optics are designed to deliver best-in-class lighting performance while offering tremendous flexibility in application. All these features, combined with Iridium²'s ease of installation and maintenance, ensure that customers enjoy low cost of ownership.

Product data

General Information		Operating and Electrical	
Lamp family code	CPO-TW [MASTER CosmoWhite CPO-TW]	Input Voltage	220 to 240 V
Gear	EB [Electronic]	Line Frequency	50 to 60 Hz
Photocell	-	Power Consumption	60 W
Product family code	SGP352 [Iridium² Medium]	Cable	-
Embedded control	-	Controls and Dimming	
CE mark	Yes	Driver/power unit/transformer	Power supply unit regulating
Light Technical		Mechanical and Housing	
Optical cover type	Flat glass	Housing Colour	Grey
Optic type outdoor	Flexible distribution version 1		

Iridium² Medium

Parts colour	All parts coloured
Approval and Application	
Protection class IEC	Safety class I
Product Data	
Order product name	SGP352 CPO-TW60W K EB FX1 AL GR
Full product name	SGP352 CPO-TW60W K EB FX1 AL GR
Full EOC	871829197569400

Order code	97569400
Material no. (12 NC)	910403998812
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291975694
Numerator – packs per outer box	1
EAN/UPC - Case	8718291975694

Dimensional drawing

