



SGS203/403

SGS203 SON-T150W 230V ST

SGS203, SON-T, 150 W, 230 V

SGS203/403 is a modular luminaire in contemporary style for safe and comfortable driving, and for area illumination, with low energy and maintenance costs. It offers a choice of canopies and a bowl or minimal-glare flat glass. Dedicated optics optimize beam control and maximize light output. Five different reflector positions allow precise control of beam direction. Energy savings are possible, for instance with the Chronosense dimming system (no pilot cable required). SGS203/403 is suitable for side-entry or post-top mounting.

Product data


General Information		Connection	
Lamp family code	SON-T [SON-T]	Cable	-
Gear	CONV [Conventional]	Mechanical and Housing	
Photocell	-	Housing Color	Grey
Product family code	SGS203 [SGS203]	Mounting device	-
Embedded control	-	Parts color	-
CE mark	Yes	Approval and Application	
ENEC mark	ENEC mark	Ingress protection code	IP43 [Wire-protected, rain/spray-proof]
Light Technical		Protection class IEC	Safety class I
Standard tilt angle posttop	5°	Product Data	
Standard tilt angle side entry	5°	Order product name	SGS203 SON-T150W 230V ST
Number of light sources	1	Full product name	SGS203 SON-T150W 230V ST
Optical cover type	Polycarbonate bowl/cover	Full product code	871155926822400
Operating and Electrical		Order code	26822400
Input Voltage	230 V	Material Nr. (12NC)	910500041312
Power Consumption	150 W		

SGS203/403

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559268224
Numerator - Packs per outer box	1

EAN/UPC - Case	8711559268224
----------------	---------------

Dimensional drawing



Product
SGS203 SON-T150W 230V ST

