



SGS203/403

SGS203 K SON-T100W I SP

SGS203, SON-T, 100 W, Safety class I

SGS203/403 is a modular luminaire in contemporary style for safe and comfortable driving, and for area illumination, with low energy and maintenance costs. It offers a choice of canopies and a bowl or minimal-glare flat glass. Dedicated optics optimize beam control and maximize light output. Five different reflector positions allow precise control of beam direction. Energy savings are possible, for instance with the Chronosense dimming system (no pilot cable required). SGS203/403 is suitable for side-entry or post-top mounting.

Product data


General Information	
Lamp family code	SON-T [SON-T]
Gear	CONV [Conventional]
Photocell	-
Product family code	SGS203 [SGS203]
Embedded control	-
CE mark	Yes
ENEC mark	ENEC mark
Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Number of light sources	1
Optical cover type	Polycarbonate bowl/cover
Optic type outdoor	-
Operating and Electrical	
Input Voltage	230 V

Power Consumption	100 W
Connection	-
Cable	-
Mechanical and Housing	
Housing Color	Grey
Mounting device	-
Parts color	-
Approval and Application	
Ingress protection code	IP43 [Wire-protected, rain/spray-proof]
Protection class IEC	Safety class I
Product Data	
Order product name	SGS203 K SON-T100W I SP
Full product name	SGS203 K SON-T100W I SP
Full product code	871155908112000
Order code	08112000

Material Nr. (12NC)	910500043312
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559081120
Numerator - Packs per outer box	1

EAN/UPC - Case	8711559081120
----------------	---------------

Dimensional drawing



Product
SGS203 K SON-T100W I SP

