



# GreenSpace Accent Cardanic

## RS343B LED27S/840 PSU-E WB II WH

GREENSPACE ACCENT CARDANIC - LED Module, system flux 2700 lm - 840 neutral white - Power supply unit external (PSU) - Wide beam - - - Safety class II - White

With the GreenSpace Accent family, retailers and building operators can now make the switch from CDM to LED and enjoy the benefits of Philips PerfectAccent light quality as well as significant energy savings – all for a reasonable initial investment. GreenSpace Accent Cardanic's regular cut-out and specific lumen packages make retrofit installation quick and easy. For fashion and food retailers, GreenSpace Accent Cardanic is available with special light flavors and LED recipes to show the clothes and fresh food produce on offer in the very best light. Check out our Fashion and Food catalogue pages to find out more about CrispWhite, PremiumWhite, Fresh Food Meat and Fresh Food Champagne.

### Product data

General information			
Number of light sources	1 [ 1 pc]	Driver included	Yes
Lamp family code	LED27S [ LED Module, system flux 2700 lm]	Optic type	WB [ Wide beam]
Beam angle of light source	120 °	Optical cover/lens type	PCO-SAT [ Polycarbonate opal satinized]
Light source colour	840 neutral white	Luminaire light beam spread	36°
Cap base	- [ -]	Connection	-
Light source replaceable	No	Cable	-
Number of gear units	1 unit	Protection class IEC	Safety class II
Gear	-	Glow-wire test	Temperature 650 °C, duration 30 s
Driver/power unit/transformer	PSU-E [ Power supply unit external (PSU)]	Flammability mark	F [ For mounting on normally flammable surfaces]
		CE mark	CE mark

# GreenSpace Accent Cardanic

ENEC mark	ENEC mark
UL mark	No
Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Constant light output	No
Spare parts available	Yes
Number of products on MCB	32
RoHS mark	RoHS mark
WEEE mark	WEEE mark
Accessory PFC	RS343Z
Product Family Code	RS343B [ GREENSPACE ACCENT CARDANIC ]

## Operating and Electrical

Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Inrush current	18.6 A
Inrush time	240 ms
Power factor (min.)	0.9

## Controls and Dimming

Dimmable	No
----------	----

## Mechanical and Housing

Housing material	Aluminium
Reflector material	Polycarbonate aluminium coated
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Optical cover/lens finish	Frosted
Overall height	135 mm
Overall diameter	190 mm
Colour	White
Dimensions (height x width x depth)	135 x NaN x NaN mm (5.3 x NaN x NaN in)

## Approval and Application

Ingress protection code	IP20 [ Finger-protected]
Mech. impact protection code	IK02 [ 0.2 J standard]

## Initial Performance (IEC Compliant)

Initial luminous flux	2800 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	119.14893617021276 lm/W
Init. Corr. colour temperature	4000 K
Init. colour rendering index	≥80
Initial chromaticity	(0.3818, 0.3797)
Initial input power	23.5 W
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

## Application Conditions

Ambient temperature range	+10 to +25 °C
Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes


## Product Data

Full product code	871869916796700
Order product name	RS343B LED27S/840 PSU-E WB II WH
EAN/UPC – product	8718699167967
Order code	16796700
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910500459502
Net weight (piece)	0.800 kg




# GreenSpace Accent Cardanic

## Dimensional drawing




GreenSpace Accent RS340B-RS343B


## Photometric data



IFAS1\_RS343B1xLED27S840WB



IFCC1\_RS343B1xLED27S840WB



IFPC1\_RS343B1xLED27S840WB

## GreenSpace Accent Cardanic

